


MAGNETIC PARTICLE CLUTCH PHC-50

MAY BE USED AS A BRAKE BY HOLDING THE FINNED BODY STATIONARY.

THE FINNED BODY ROTATES WITH THE INPUT SHAFT.
 HOLD THE WIRES STATIONARY BY THE 2 SLOTTED TABS.
 THE 30mm BORE IS COUPLED TO THE INPUT SHAFT WITH ELECTRICAL EXCITATION.



Units : inches
 Scale : 1/3

Drawn 11/6/06
 Changed 3/27/14

Lake Placid, NY USA
 Telephone 518 523-2422
 www.placidindustries.com

