


# MAGNETIC PARTICLE CLUTCH PHC-50

MAY BE USED AS A BRAKE BY HOLDING THE FINNED BODY STATIONARY.

THE FINNED BODY ROTATES WITH THE INPUT SHAFT.  
 HOLD THE WIRES STATIONARY BY THE 2 SLOTTED TABS.  
 THE 30mm BORE IS COUPLED TO THE INPUT SHAFT WITH ELECTRICAL EXCITATION.



Units : inches  
 Scale : 1/3

Drawn 11/6/06  
 Changed 3/27/14

Elmira, NY 14901 USA  
 Telephone: 518-523-2422  
 www.placidindustries.com

